



PL-Q 4 Pin

PL-Q 21W/830/4P 1CT/10 BOX

PL-Q is an efficient, square-shaped compact fluorescent lamp, typically used in decorative-lighting luminaires. While offering the advantage of energy-efficient operation, it also provides design freedom for flat ceiling or wall fixtures in particular, due to its low built-in height and uniform spread of light. The 4-pin version is designed for operation on electronic gear.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	GR10Q [GR10q]
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,400 lumen
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	66.6 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	21.0 W


Lamp Current (Nom)	0.260 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Max)	3.0 mg
Energy Consumption kWh/1000 h	23 kWh
Product Data	
Full product code	871869666351600
Order product name	PL-Q 21W/830/4P 1CT/10 BOX
Order code	927938383040
Numerator - Quantity Per Pack	1

PL-Q 4 Pin

Numerator - Packs per outer box	10
Material Nr. (12NC)	927938383040
Full product name	PL-Q 21W/830/4P 1CT/10 BOX
EAN/UPC - Case	8718696663523


EAN/UPC - Product/Case	8718696663516
------------------------	---------------

Dimensional drawing



Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 21W/830/4P 1CT/10 BOX	40 mm	15 mm	27.5 mm	141 mm	49 mm	41 mm	138 mm

Photometric data




Spectral Power Distribution Colour - PL-Q 21W/830/4P 1CT/10 BOX

Lifetime




Lumen Maintenance Diagram - PL-Q 21W/830/4P 1CT/10 BOX



Life Expectancy Diagram - PL-Q 21W/830/4P 1CT/10 BOX

PL-Q 4 Pin

Lifetime



Life Expectancy Diagram - PL-Q 21W/830/4P 1CT/10 BOX

