



PL-Q 4 Pin



PL-Q 16W/827/4P 1CT/10

Compact fluorescent lamps with a quadrant-like shape

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	GR10Q [GR10q]
Flux measurement reference	Sphere
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,050 lm
Color Designation	Incandescent White
Chromaticity Coordinate X (Nom)	0.463
Chromaticity Coordinate Y (Nom)	0.42
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	66.6 lm/W
Color rendering index (CRI)	81
Operating and Electrical	
Power Consumption	16.2 W
Lamp Current (Nom)	0.195 A

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	3 mg
Mercury (Hg) Content (Nom)	4 mg
Energy Consumption kWh/1000 h	17 kWh
EPREL Registration Number	423606
Product Data	
Order product name	PL-Q 16W/827/4P 1CT/10BOX
Full product name	PL-Q 16W/827/4P 1CT/10
Full product code	871150026988125
Order code	26988125
Material Nr. (12NC)	927939182740
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500269881

PL-Q 4 Pin


Numerator - Packs per outer box	10
EAN/UPC - Case	8711500270023

Dimensional drawing




Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 16W/827/4P 1CT/10BOX	40 mm	13.7 mm	27.5 mm	138 mm	49 mm	40.5 mm	135 mm

Photometric data




Spectral Power Distribution Colour - PL-Q 16W/827/4P 1CT/10BOX

Lifetime



Lumen Maintenance Diagram - PL-Q 16W/827/4P 1CT/10BOX



Life Expectancy Diagram - PL-Q 16W/827/4P 1CT/10BOX

PL-Q 4 Pin

Lifetime



Life Expectancy Diagram - PL-Q 16W/827/4P 1CT/10BOX

