



MASTER TL5 Circular

MASTER TL5 Circular 40W/830 1CT/10

16 mm tube diameter circular fluorescent lamps with a choice of various diameters

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	2GX13 [2GX13]
Flux measurement reference	Sphere
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	3,300 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	83 lm/W
Color rendering index (CRI)	81
Operating and Electrical	
Power Consumption	40.5 W
Lamp Current (Nom)	0.320 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	C-T5 [C-T5 16 mm]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	4 mg
Mercury (Hg) Content (Nom)	4 mg
Energy Consumption kWh/1000 h	41 kWh
EPREL Registration Number	423620
Product Data	
Order product name	MASTER TL5 Circular 40W/830 1CT/10
Full product name	MASTER TL5 Circular 40W/830 1CT/10
Full product code	871150064097025
Order code	927965583013
Material Nr. (12NC)	927965583013
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500640970
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500640987


MASTER TL5 Circular

Dimensional drawing




Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 40W/830	18 mm	14 mm	293 mm	305 mm	260 mm	272 mm
1CT/10						

Photometric data




Spectral Power Distribution Colour - MASTER TL5 Circular 40W/830 1CT/10

Lifetime




Life Expectancy Diagram - MASTER TL5 Circular 40W/830 1CT/10



Life Expectancy Diagram - MASTER TL5 Circular 40W/830 1CT/10

MASTER TL5 Circular

Lifetime



Lumen Maintenance Diagram - MASTER TL5 Circular 40W/830 1CT/10

