



# MASTER TL-D Xtreme

## MASTER TL-D Xtreme 58W/865 1SL/25

Low-pressure mercury discharge lamp with a tubular 26mm envelope

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 50% failures (nom.)	47000 h
Life to 50% failures preheat (nom.)	79000 h
LSF 2000 h Rated	100 %
LSF 4000 h Rated	99 %
LSF 6000 h Rated	99 %
LSF 8000 h Rated	99 %
LSF 12000 h Rated	99 %
LSF 16000 h Rated	99 %
LSF 20000 h Rated	99 %

Light Technical	
Colour code	865 [ CCT of 6,500 K]
Luminous flux (nom.)	5000 lm
Luminous flux (rated) (nom.)	5000 lm
Colour designation	Cool Daylight
Correlated Colour Temperature (Nom)	6500 K
Luminous efficacy (rated) (nom.)	86 lm/W
Color rendering index (nom.)	>80
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %

LLMF 20000 h Rated	90 %
--------------------	------

Operating and Electrical	
Power (Rated) (Nom)	58.5 W
Lamp current (nom.)	0.665 A

Temperature	
Design temperature (nom.)	25 °C

Controls and Dimming	
Dimmable	yes

Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	3.0 mg
Energy Consumption kWh/1000 h	68 kWh

Product Data	
Full product code	871150089279940
Order product name	MASTER TL-D Xtreme 58W/865 SLV
EAN/UPC – product	8711500892799
Order code	89279940
Local Code	58865XTREME
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (I2NC)	927983386514

# MASTER TL-D Xtreme

Net weight (piece)	167.000 g
ILCOS Code	FD-58/65/1B-E-G13



## Warnings and Safety

## Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtreme 58W/865 SLV	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

### TL-D Xtreme 58W/865



## Photometric data



### Lightcolour /865

### Lightcolour /865

## Lifetime





### LDLE\_TL-D8LL\_0001-Life expectancy diagram

### LDLE\_TL-D8LL\_0002-Life expectancy diagram

# MASTER TL-D Xtreme

## Lifetime



LDLE\_TL-D8LL\_0003-Life expectancy diagram

LDLM\_TL-D8LL\_0001-Lumen maintenance diagram

