



# MASTER TL5 High Efficiency Eco

## MASTER TL5 HE Eco 25=28W/830 UNP/40

This extremely efficient TL5 lamp (tube diameter 16 mm) saves considerable energy by simple lamp-for-lamp replacement. The TL5 HE Eco lamp offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

### Product data

General Information	
Cap-Base	G5 [ G5]
Life to 50% Failures Preheat (Nom)	25000 h
Features	na [ Not Applicable]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	99 %
LSF Preheat 20000 h Rated	94 %
Light Technical	
Color Code	830 [ CCT of 3000K]
Luminous Flux (Nom)	2900 lm
Luminous Flux (Rated) (Nom)	2600 lm
Color Designation	Warm White (WW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	114 lm/W
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	103 lm/W
Color Rendering Index (Max)	85
Operating and Electrical	
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %
Power (Nom)	25.2 W
Lamp Current (Nom)	0.170 A
Temperature	
Design Temperature (Nom)	35 °C
Controls and Dimming	
Dimmable	Yes

# MASTER TL5 High Efficiency Eco

## Approval and Application

Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	28 kWh


## Product Data

Full product code	872790082588600
Order product name	MASTER TL5 HE Eco 25=28W/830 UNP/40

EAN/UPC - Product	8711500880000
Order code	927990983031
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927990983031
Net Weight (Piece)	105.800 g
ILCOS Code	FDH-25/30/1B-L/P-G5-16/1150

## Warnings and Safety

## Dimensional drawing




## Product


MASTER TL5 HE Eco 25=28W/830 UNP/40

## TL5 HE Eco 25=28W/830

## Photometric data



LDPB\_TL5HEECO\_830-Spectral power distribution B/W



LDPO\_TL5HEECO\_830-Spectral power distribution Colour

# MASTER TL5 High Efficiency Eco

## Lifetime



LDLE\_TL5HEECO\_0001-Life expectancy diagram

LDLE\_TL5HEECO\_0002-Life expectancy diagram



LDLM\_TL5HEECO\_0001-Lumen maintenance diagram

