



# T5 High Output Energy Advantage

## F54T5/841/HO/EA/ALTO 49W 40/1

Philips Energy Advantage T5 HO 49W lamps are environmentally-responsible, ultra-slim and have extraordinary light output with increased energy savings.

### Product data

General Information	
Base	G5 [ G5]
Life to 50% Failures Preheat (Nom)	30000 h
Features	HO EA [ High Output Energy Advantage]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	99 %
LSF Preheat 20000 h Rated	94 %
Light Technical	
Color Code	841 [ CCT of 4100K]
Initial lumen (Nom)	5000 lm
Luminous Flux (Rated) (Nom)	4450 lm
Color Designation	Cool White (CW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	102 lm/W
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	93 lm/W
Color Rendering Index (Max)	85
Color Rendering Index (Min)	80

Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

### Operating and Electrical

Power (Rated) (Nom)	48.0 W
Lamp Current (Nom)	0.460 A

### Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

### Controls and Dimming

Dimmable	Yes
----------	-----

### Approval and Application

Energy Efficiency Label (EEL)	A
-------------------------------	---

## T5 High Output Energy Advantage

Mercury (Hg) Content (Nom)	1.4 mg
<b>Product Data</b>	
Order product name	F54T5 841 HO EA ALTO 49W
EAN/UPC - Product	046677220525
Order code	220525

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927991984031
Net Weight (Piece)	104.500 g


### Warnings and Safety

### Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
F54T5 841 HO EA ALTO 49W	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

TL5 HO Eco F54T5/841 HO EA 49W

### Photometric data



LDPB\_TL5ECO\_841-Spectral power distribution B/W

LDPO\_TL5ECO\_841-Spectral power distribution Colour

# T5 High Output Energy Advantage

## Lifetime



LDLE\_TL5ECO\_0001-Life expectancy diagram

LDLE\_TL5ECO\_0002-Life expectancy diagram



LDLM\_TL5ECO\_0001-Lumen maintenance diagram

