



TL Mini Standard Colours

TL Mini 6W/33-640 na FAM/10X25BOX

This TL Miniature lamp (tube diameter 16 mm) is a lamp with small dimensions, which enables system miniaturization and offers the possibility of operation on low-voltage DC supply. It is ideal for applications where space is limited but where color rendering and efficacy are not the most important factors, such as orientation, signage and emergency lighting.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information				
Cap-Base	G5			
Flux measurement reference	Sphere			
Life to 50% Failures (Nom)	10,000 hour(s)			
Light Technical				
Color Code	33-640			
Luminous Flux	260 lm			
Color Designation	Cool White (CW)			
Chromaticity Coordinate X (Nom)	0.38			
Chromaticity Coordinate Y (Nom)	0.38			
Correlated Color Temperature (Nom)	4000 K			
Luminous Efficacy (rated) (Nom)	43 lm/W			
Color rendering index (CRI)	59			

Operating and Electrical	
Power Consumption	6.0 W
Lamp Current (Nom)	0.160 A
Voltage (Nom)	42 V
Voltage (Nom)	42 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2.5 mg


Datasheet, 2023, April 16 data subject to change

TL Mini Standard Colours

Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	6 kWh
EPREL Registration Number	423488
Product Data	
Order product name	TL Mini 6W/33-640 FAM/10X25BOX
Full product name	TL Mini 6W/33-640 na FAM/10X25BOX
Full product code	871150071583827


Order code	71583827
Material Nr. (12NC)	928000503340
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500715838
Numerator - Packs per outer box	250
EAN/UPC - Case	8711500715852

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 6W/33-640 FAM/	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm
10X25BOX					

Photometric data



Spectral Power Distribution Colour - TL Mini 6W/33-640 FAM/10X25BOX



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.