



# MASTER TL-E Circular Super 80

## TL-E 22W/840 1CT/12

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Color rendering index (CRI)	
Cap-Base	G10Q [G10q]	80	
Flux measurement reference	Sphere		
Life to 50% Failures (Nom)	13,000 hour(s)		
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power Consumption	22.2 W
Luminous Flux	1,285 lm	Lamp Current (Nom)	0.400 A
Color Designation	Cool White (CW)	Voltage (Nom)	62 V
Chromaticity Coordinate X (Nom)	0.38	Voltage (Nom)	62 V
Chromaticity Coordinate Y (Nom)	0.38	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	59 lm/W		


# MASTER TL-E Circular Super 80

Mechanical and Housing	
Bulb Shape	C-T9 [C-T9 29 mm]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	8 mg
Mercury (Hg) Content (Nom)	8 mg
Energy Consumption kWh/1000 h	23 kWh
EPREL Registration Number	423506

Product Data	
Order product name	TL-E 22W/840 1CT/12


Full product name	TL-E 22W/840 1CT/12
Full product code	872790084050600
Order code	928026284070
Material Nr. (12NC)	928026284070
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900840506
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900840513

## Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 22W/840 1CT/12	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm

## Photometric data



Spectral Power Distribution Colour - TL-E 22W/840 1CT/12

## MASTER TL-E Circular Super 80

