



TL-D Standard Colours

TL-D 18W/33-640 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- · Lamp contains mercury.
- · Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information				
Cap-Base	G13 [Medium Bi-Pin Fluorescent]			
Life to 50% Failures (Nom)	13,000 hour(s)			
Light Technical				
Color Code	33-640			
Luminous Flux	1,200 lm Cool White (CW) 4100 K			
Color Designation				
Correlated Color Temperature (Nom)				
Color rendering index (CRI)	63			
Operating and Electrical				
Power Consumption	18.0 W			
Lamp Current (Nom)	0.360 A			
Voltage (Nom)	59 V			

Voltage (Nom)	59 V			
Controls and Dimming				
Dimmable	Yes			
Mechanical and Housing				
Bulb Shape	T8 [26 mm (T8)]			
Approval and Application				
Mercury (Hg) Content (Nom)	5.0 mg			
Energy Consumption kWh/1000 h	22 kWh			
Product Data				
Order product name	TL-D 18W/33-640 1SL/25			
Full product name	product name TL-D 18W/33-640 1SL/25			


Datasheet, 2023, September 19 data subject to change

TL-D Standard Colours

Full product code	871150095041340		
Order code	251470		
Material Nr. (12NC)	928048003312		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8711500950413		


Numerator - Packs per outer box	25	
EAN/UPC - Case	8711500950420	

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/33-640	1-1/8 inch	23-1/4 inch	23-1/2 inch	23-7/16 inch	23-13/16 inch
1SL/25					


Photometric data



Spectral Power Distribution Colour - TL-D 18W/33-640 1SL/25

Lifetime






Life Expectancy Diagram - TL-D 18W/33-640 1SL/25

Life Expectancy Diagram - TL-D 18W/33-640 1SL/25

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 18W/33-640 1SL/25

