



Actinic BL TL-D(K) Secura

Actinic BL TL-D 18W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		UV Depreciation at 5000 h	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		30 %
Life to 50% Failures (Nom)	13,000 h	Operating and Electrical	
Useful Life (Nom)	9,000 h	Power Consumption	18 W
		Lamp Current (Nom)	0.36 A
Light Technical		Voltage (Nom)	59 V
Color Code	10	Voltage (Nom)	59 V
Color Designation	Actinic	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	220	Bulb Shape	T26
Chromaticity Coordinate Y (Nom)	200		
UV Depreciation at 2000 h	20 %		

Actinic BL TL-D(K) Secura

Approval and Application

Mercury (Hg) Content (Nom) 5.0 mg

UV

UV-A Radiation 100Hr (IEC) 4.5 W

Product Data

Order product name Actinic BL TL-D 18W/10 Secura 1SL/25
 Full product name Actinic BL TL-D 18W/10 Secura 1SL/25
 Full product code 872790085383400

Local code description TLD18W10SECURA

Order code 928048201003

Material Nr. (12NC) 928048201003

Local order code TLD18W10SECURA


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8727900853834

Numerator - Packs per outer box 25


EAN/UPC - Case 8727900853841

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 18W/10 Secura 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data



Spectral Power Distribution Colour - Actinic BL TL-D 18W/10 Secura 1SL/25

