

TL-D Standard Colours

TL-D 36W/54-765 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information				
Cap-Base	G13 [Medium Bi-Pin Fluorescent			
Life to 50% Failures (Nom)	13,000 hour(s)			
Light Technical				
Color Code	54-765			
Luminous Flux	2,500 lm			
Color Designation	Cool Daylight			
Correlated Color Temperature (Nom)	6200 K			
Color rendering index (CRI)	72			
Operating and Electrical				
Power Consumption	36.0 W			
Lamp Current (Nom)	0.440 A			
Voltage (Nom)	103 V			
Voltage (Nom)	103 V			

Controls and Dimming			
Dimmable	Yes		
Mechanical and Housing			
Bulb Shape	Т8		
Approval and Application			
Mercury (Hg) Content (Nom)	5.0 mg		
Energy Consumption kWh/1000 h	43 kWh		
Product Data			
Order product name	TL-D 36W/54-765 1SL/25		
Full product name	TL-D 36W/54-765 1SL/25		
Full product code	694793919444500		
Order code	928048505453		
Material Nr. (12NC)	928048505453		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	6947939194445		

TL-D Standard Colours


Numerator - Packs per outer box	25
EAN/UPC - Case	6922341996351

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/54-765 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm


Photometric data



Spectral Power Distribution Colour - TL-D 36W/54-765 1SL/25

Lifetime






Life Expectancy Diagram - TL-D 36W/54-765 1SL/25

Life Expectancy Diagram - TL-D 36W/54-765 1SL/25

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 36W/54-765 1SL/25



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, January 12 - data subject to change