



TUV T8

TUV 75W HO 1SL/6

TUV T8 lamps are double-ended UV-C 253.7 nm emitting lamps. TUV T8 lamps offer almost constant UV-C output over their complete lifetime. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- · Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

Product data

General Information				
Cap-Base	G13 [Medium Bi-Pin Fluorescent]			
Useful Life (Nom)	9,000 hour(s)			
Light Technical				
Color Code	TUV			
Color Designation	- [Not Specified]			
Depreciation at Useful Lifetime	15 %			
Operating and Electrical				
Power Consumption	75 W			
Lamp Current (Nom)	0.835 A			
Voltage (Nom)	110 V			
Voltage (Nom)	110 V			

Mechanical and Housing	
Bulb Shape	T26
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
UV	
UV-C Radiation at 100 hr	27.8 W
Product Data	
Order product name	TUV 75W HO 1SL/6
Full product name	TUV 75W HO 1SL/6
Full product code	871150061851110
Order code	928049404003
Material Nr. (12NC)	928049404003


Datasheet, 2024, January 29 data subject to change

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500618511
Numerator - Packs per outer box	6


EAN/UPC - Case 8711500618528

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV 75W HO 1SL/6	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm



Photometric data



Spectral Power Distribution Colour - TUV 75W HO 1SL/6



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.