



TUV T8

TUV TL-D 95W HO SLV/25

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data

General Information		
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	
Useful Life (Nom)	8,000 h	
Light Technical		
Color Code	TUV	
Color Designation	- [Not Specified]	
Depreciation at Useful Lifetime	15 %	
Operating and Electrical		
Power Consumption	60 W	
Lamp Current (Nom)	0.620 A	
Voltage (Nom)	124 V	

Voltage (Nom)	124 V	
Mechanical and Housing		
Bulb Shape	T26	
Approval and Application		
Mercury (Hg) Content (Nom)	8.0 mg	
UV		
UV-C Radiation at 100 hr	22.5 W	
Product Data		
Order product name	TUV TL-D 95W HO SLV/25	
Full product name	TUV TL-D 95W HO SLV/25	

Datasheet, 2023, April 14 data subject to change


TUV T8

Full product code	871150089392540	
Local code description	TUV95W	
Order code	928049804006	
Material Nr. (12NC)	928049804006	
Local order code	TUV95W	
Numerator - Quantity Per Pack	1	


EAN/UPC - Product/Case	8711500893925	
Numerator - Packs per outer box	25	
EAN/UPC - Case	8711500893932	

Dimensional drawing

	/	
<u>a</u>	//	
	A	
	В	
	С	



Photometric data



Spectral Power Distribution Colour - TUV TL-D 95W HO SLV/25



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.