



# MASTERColour CDM-R Elite

## MASTERColour CDM-R Elite 70W/942 E27 PAR30L 40D

Compact, very high-efficiency, long-life Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high color rendering

### Warnings and Safety

- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information			
Cap-Base	E27	Chromaticity Coordinate Y (Nom)	0.366
Operating Position	UNIVERSAL [Any or Universal (U)]	Correlated Color Temperature (Nom)	4200 K
Switching Cycle	1,350	Luminous Efficacy (rated) (Nom)	71 lm/W
Flux measurement reference	Narrow Cone	Color rendering index (CRI)	92
Life to 50% Failures (Nom)	15,000 hour(s)	LLMF At End Of Nominal Lifetime (Nom)	75 %
Light Technical		Luminous Flux in 90° Cone (Rated)	4,500 lm
Color Code	942 [CCT of 4200K]	Operating and Electrical	
Beam Angle (Nom)	40 degree(s)	Power Consumption	73.2 W
Luminous Flux	4,500 lm	Warm-up time to 60% light	120 s
Luminous Intensity (Nom)	9,800 cd	Voltage (Nom)	90 V
Color Designation	Cool White (CW)	Voltage (Nom)	90 V
Chromaticity Coordinate X (Nom)	0.371		

MASTERColour CDM-R Elite

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	PAR30L
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	6.6 mg
Mercury (Hg) Content (Nom)	6.5 mg
Energy Consumption kWh/1000 h	74 kWh
EPREL Registration Number	473306


Product Data	
Order product name	MC CDM-R Elite 70W/942 E27 PAR30L 40D
Full product name	MASTERColour CDM-R Elite 70W/942 E27 PAR30L 40D
Full product code	871829165169700
Order code	65169700
Material Nr. (12NC)	928053100630
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291651697
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291651703

Dimensional drawing




Product	D (max)	C (max)
MC CDM-R Elite 70W/942 E27 PAR30L 40D	97 mm	123 mm

Photometric data




Spectral Power Distribution Colour - MC CDM-R Elite 70W/942 E27 PAR30L 40D




Light Distribution Diagram - MC CDM-R Elite 70W/942 E27 PAR30L 40D

MASTERC colour CDM-R Elite

Lifetime



Life Expectancy Diagram - MC CDM-R Elite 70W/942 E27 PAR30L 40D



Lumen Maintenance Diagram - MC CDM-R Elite 70W/942 E27 PAR30L 40D

