



# MASTERColour CDM-TC Elite

## MASTERColour CDM-TC Elite 50W/942 G8.5 1CT

Compact, single-ended, very high-efficiency, long-life ceramic metal-halide discharge lamp producing crisp white sparkling light with high color rendering

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Color rendering index (CRI)	
Cap-Base	G8.5 [G8.5]		90
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	7.1 mm
Flux measurement reference	Sphere	Operating and Electrical	
Life to 50% Failures (Nom)	15,000 hour(s)	Power Consumption	50.2 W
Light Technical		Voltage (Nom)	93 V
Color Code	942 [CCT of 4200K]	Voltage (Nom)	93 V
Luminous Flux	5,050 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Chromaticity Coordinate X (Nom)	0.371	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	0.366	Bulb Finish	Clear
Correlated Color Temperature (Nom)	4200 K		
Luminous Efficacy (rated) (Nom)	101 lm/W		

# MASTERC colour CDM-TC Elite


Bulb Shape	T14 [T 14 mm]
<b>Approval and Application</b>	
Energy Efficiency Class	F
Mercury (Hg) Content (Max)	5.7 mg
Mercury (Hg) Content (Nom)	5.7 mg
Energy Consumption kWh/1000 h	51 kWh
EPREL Registration Number	473323

## Product Data

Order product name	MASTERC CDM-TC Elite 50W/942 G8.5 ICT
--------------------	---------------------------------------



Full product name	MASTERC colour CDM-TC Elite 50W/942 G8.5 ICT
Full product code	871829120163200
Order code	20163200
Material Nr. (12NC)	928080115131
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291201632
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291201649

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 50W/942 G8.5 ICT	15 mm	7.1 mm	51 mm	53 mm	52 mm	85 mm

## Photometric data





Light Distribution Diagram - MASTERC CDM-TC Elite 50W/942 G8.5 ICT

Spectral Power Distribution Colour - MASTERC CDM-TC Elite 50W/942 G8.5 ICT

# MASTERC colour CDM-TC Elite

## Lifetime



Life Expectancy Diagram - MASTERC CDM-TC Elite 50W/942 G8.5 1CT

Lumen Maintenance Diagram - MASTERC CDM-TC Elite 50W/942 G8.5 1CT

