



MASTER CityWhite CDO-TT

MASTER CityWh CDO-TT Plus 150W/828 E40

Ceramic metal halide lamp with clear tubular outer bulb shape, used in outdoor offering pleasant white light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)

Product data

General Information	
Cap-Base	E40
Operating Position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	27,000 h
Light Technical	
Color Code	828 [CCT of 2800K]
Luminous Flux	16,400 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.447
Chromaticity Coordinate Y (Nom)	0.4
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color rendering index (CRI)	87
Arc Length O (Nom)	10 mm


Operating and Electrical	
Power Consumption	148.5 W
Voltage (Nom)	99 V
Voltage (Nom)	99 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T46
Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) Content (Max)	15.8 mg
Mercury (Hg) Content (Nom)	15.8 mg
Energy Consumption kWh/1000 h	149 kWh

MASTER CityWhite CDO-TT

EPREL Registration Number	473327
Product Data	
Order product name	MASTER CityWh CDO-TT Plus 150W/828 E40
Full product name	MASTER CityWh CDO-TT Plus 150W/828 E40
Full product code	871829112034600
Local code description	CDOTT150W828
Order code	928082219231


Material Nr. (12NC)	928082219231
Local order code	CDOTT150W828
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291120346
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291120353

Dimensional drawing




Product	D (max)	O	L	C (max)
MASTER CityWh CDO-TT Plus 150W/828 E40	47 mm	10 mm	132 mm	211 mm

Photometric data




Light Distribution Diagram - MASTER CityWh CDO-TT Plus 150W/828 E40




Spectral Power Distribution Colour - MASTER CityWh CDO-TT Plus 150W/828 E40

MASTER CityWhite CDO-TT

Lifetime



Life Expectancy Diagram - MASTER CityWh CDO-TT Plus 150W/828 E40



Lumen Maintenance Diagram - MASTER CityWh CDO-TT Plus 150W/828 E40

