



# MASTERColour CDM-TP

## MASTERColour CDM-TP 150W/942 PGX12-2 1CT/12

Range of protected, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light to be used in open luminaires

### Warnings and Safety

- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Arc Length O (Nom)	
Cap-Base	PGX12-2 [PGX12-2]	8 mm	
Operating Position	UNIVERSAL [Any or Universal (U)]		
Life to 50% Failures (Nom)	16,000 hour(s)		
Light Technical		Operating and Electrical	
Color Code	942 [CCT of 4200K]	Power Consumption	150.1 W
Color Designation	Cool White (CW)	Voltage (Nom)	96 V
Chromaticity Coordinate X (Nom)	376	Voltage (Nom)	96 V
Chromaticity Coordinate Y (Nom)	374		
Correlated Color Temperature (Nom)	4200 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	83 lm/W	Dimmable	No
Color rendering index (CRI)	95	Mechanical and Housing	
		Bulb Finish	Clear
		Bulb Shape	T31 [T 31mm]

# MASTERC colour CDM-TP

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Nom)	12.2 mg
Energy Consumption kWh/1000 h	165 kWh
Product Data	
Order product name	MASTERC CDM-TP 150W/942 PGX12-2 1CT/12
Full product name	MASTERC colour CDM-TP 150W/942 PGX12-2 1CT/12


Full product code	871150020111915
Order code	20111915
Material Nr. (12NC)	928086209230
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500201119
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500201126

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TP 150W/942 PGX12-2 1CT/12	32.00 mm	8 mm	89 mm	93 mm	91 mm	149 mm


## Photometric data



Spectral Power Distribution Colour - MASTERC CDM-TP 150W/942 PGX12-2 1CT/12

MASTERC colour CDM-TP

Lifetime



Life Expectancy Diagram - MASTERC CDM-TP 150W/942 PGX12-2 1CT/12

Lumen Maintenance Diagram - MASTERC CDM-TP 150W/942 PGX12-2 1CT/12

