



CosmoPolis CosmoWhite

CPO-TW 140W/728 White PGZ12

Philips Cosmopolis Outdoor Lighting System simplifies outdoor lighting with the combination of a miniature lamp and an optimized electronic ballast system.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	PGZ12
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	30,000 hour(s)
Light Technical	
Color Code	728 [CCT of 2800K]
Color Designation	White (WH)
Chromaticity Coordinate X (Nom)	440
Chromaticity Coordinate Y (Nom)	413
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	72

Arc Length O (Nom)	22 mm
Operating and Electrical	
Power Consumption	141.0 W
Voltage (Nom)	94 V
Voltage (Nom)	94 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

CosmoPolis CosmoWhite

Bulb Shape	T19
------------	-----

Approval and Application


Mercury (Hg) Content (Nom)	3.9 mg
Energy Consumption kWh/1000 h	154 kWh

Product Data

Order product name	CPO-TW 140W/728 White PGZ12
Full product name	CPO-TW 140W/728 White PGZ12


Order code	157321
Material Nr. (12NC)	928088805105
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677157326
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677157321

Dimensional drawing




Product	D (max)	D	O	L	C (max)
CPO-TW 140W/728 White PGZ12	13/16 inch	3/4 inch	7/8 inch	2-5/8 inch	5-15/16 inch

Photometric data




Light Distribution Diagram - CPO-TW 140W/728 White PGZ12




Spectral Power Distribution Colour - CPO-TW 140W/728 White PGZ12

Lifetime



Life Expectancy Diagram - CPO-TW 140W/728 White PGZ12



Lumen Maintenance Diagram - CPO-TW 140W/728 White PGZ12

