

MASTERColour CDM-TC

MASTERC CDM-TC 35W/842 G8.5 1CT/12

Range of single-ended, very compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G8.5 [G8.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	12,000 hour(s)

Light Technical	
Color Code	842 [CCT of 4200K]
Luminous Flux	3,100 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.371
Chromaticity Coordinate Y (Nom)	0.366
Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	79 lm/W
Color rendering index (CRI)	85
Arc Length O (Nom)	5 mm

Operating and Electrical	
Power Consumption	39.1 W
Voltage (Nom)	85 V
Voltage (Nom)	85 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	UV-Block Quartz

MASTERColour CDM-TC

Bulb Shape	T14 [T 14 mm]

Approval and Application


Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2.7 mg
Mercury (Hg) Content (Nom)	2.7 mg
Energy Consumption kWh/1000 h	40 kWh
EPREL Registration Number	473352

Product Data

Order product name	MASTERC CDM-TC 35W/842 G8.5 1CT/12

Full product name	MASTERC CDM-TC 35W/842 G8.5 1CT/12
Full product code	871150020957315
Order code	928093805125
Material Nr. (12NC)	928093805125
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500209573
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500209580

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC 35W/842 G8.5 1CT/12	15 mm	0.5 inch	5 mm	51 mm	53 mm	52 mm	85 mm


Photometric data



Spectral Power Distribution Colour - MASTERC CDM-TC 35W/842 G8.5 1CT/12

MASTERColour CDM-TC

Lifetime



Life Expectancy Diagram - MASTERC CDM-TC 35W/842 G8.5 1CT/12

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.