



MSR Hot Restrike

MSR 200 HR 1CT/4

High-efficiency hot restrike metal halide lamps designed for optimum light collection

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information					
Cap-Base	GZY9.5 [GZY9.5]				
Operating Position	UNIVERSAL [Any or Universal (U)]				
Life to 50% Failures (Nom)	200 h				
Light Technical					
Color Code	- [Not Specified]				
Luminous Flux (Min)	12,000 lm				
Luminous Flux	15,000 lm				
Chromaticity Coordinate X (Nom)	325				
Chromaticity Coordinate Y (Nom)	323				
Correlated Color Temperature (Nom)	6000 K				
Luminous Efficacy (rated) (Nom)	75 lm/W				
Color rendering index (CRI)	92				
Arc Length O (Nom)	5.0 mm				
Operating and Electrical					
Power Consumption	200 W				
Lamp Current (Nom)	3.3 A				

Controls and Dimming					
Dimmable	Yes				
Product Data					
Order product name	MSR 200 HR 1CT/4				
Full product name	MSR 200 HR 1CT/4				
Full product code	871869641604400				
Local code description	MSR200HR				
Order code	928097905115				
Material Nr. (12NC)	928097905115				
Local order code	MSR200HR				
Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	8718696416044				
Numerator - Packs per outer box	4				
EAN/UPC - Case	8718696416051				


MSR Hot Restrike

Dimensional drawing



Product	D (max)	0	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 200	20 mm	5.0	38 mm	40 mm	39	80 mm	24 mm	23.5	23 mm
HR 1CT/4		mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSR 200 HR 1CT/4



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 16 - data subject to change