



MSR Gold™ SA Double Ended

MSR Gold™ 1200 SA/DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	SFC10-4 [SFC10-4]
Operating position	UNIVERSAL [Any or Universal (U)]
Life to 50% failures (nom.)	750 h
Light Technical	
Colour Code	- [Not Specified]
Luminous Flux	103,000 lm
Chromaticity Coordinate X (Nom)	326
Chromaticity Coordinate Y (Nom)	332
Correlated Colour Temperature	6000 K
Luminous efficacy (rated) (min.)	77 lm/W
Luminous efficacy (rated) (nom.)	86 lm/W

Colour rendering index (CRI)	83
Arc Length O (Nom)	7.0 mm
Operating and Electrical	
Power Consumption	1,200 W
Lamp current (nom.)	13.6 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSR Gold 1200 SA/DE 1CT/4
Full product name	MSR Gold™ 1200 SA/DE 1CT/4


Datasheet, 2023, April 16 data subject to change

MSR Gold™ SA Double Ended

Full EOC	871829122121000
Order code	22121000
Material no. (12 NC)	928099605115
Local order code	MSR1200SADE
SAP numerator – quantity per pack	1


EAN/UPC — Product/Case	8718291221210
Numerator – packs per outer box	4
EAN/UPC - Case	8718291221227

Dimensional drawing





Photometric data



Spectral Power Distribution Colour - MSR Gold 1200 SA/DE 1CT/4



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.