



# TUV Dynapower system

## TUV 260W XPT DIM HO UNP/20

Philips Dynapower system consists of an electronic DynaPower driver that operates one or two TUV Amalgam 230W, 260W and 335W XPT lamps. This system is extremely reliable and robust. The driver allows for immediate energy savings compared to similar drivers on the market. Moreover, it can be dimmed down to 60% power level for additional energy savings. Further energy savings are realized by the TUV Amalgam XPT lamps, because they can be dimmed down to reach the same UV output as similar lamps on the market.

#### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation
- · Lamp contains mercury.
- · Manage in Accord with Disposal Laws.
- · See: www.lamprecycle.org or 1-800-555-0050

#### **Product data**

General Information		
Cap-Base	G5.4X17Q [G5.4x17q]	
Operating Position	UNIVERSAL [Any or Universal (U)]	
Useful Life (Nom)	12,000 hour(s)	
Light Technical		
Depreciation at Useful Lifetime	10 %	
epi delation at obelat Elictime		

Arc Length O (Nom)	1,400 mm	
Operating and Electrical		
Power Consumption	260 W	
Lamp Current (Nom)	2.7 A	


Datasheet, 2023, September 7 data subject to change

# **TUV** Dynapower system

Controls and Dimming			
Dimmable	Yes		
UV			
UV-C Radiation at 100 hr	98 W		
Product Data			
Order product name	TUV 260W XPT HO DIM UNP/20		
Full product name	TUV 260W XPT DIM HO UNP/20		


Full product code	871869645296700	
Order code	300665	
Material Nr. (12NC)	928104405112	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8718696452967	
Numerator - Packs per outer box	20	
EAN/UPC - Case	8718696452974	

## Dimensional drawing



Product	D	0	C (max)
TUV 260W XPT HO DIM UNP/20	1-1/4 inch	55-1/8 inch	59-11/16 inch


## Photometric data



Spectral Power Distribution Colour - TUV 260W XPT HO DIM UNP/20

## **TUV Dynapower system**

## Lifetime



Lumen Maintenance Diagram - TUV 260W XPT HO DIM UNP/20



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.