



MASTER SON-T APIA Plus Xtra



MASTER SON-T APIA Plus Xtra 400W E40 1SL/12

High Pressure Sodium lamp with clear tubular outer bulb shape, high output and longest reliable lifetime

Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- HF gear must comply with Philips LDi guideline
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	E40
Operating Position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	45,000 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux	55,400 lm
Chromaticity Coordinate X (Nom)	0.535
Chromaticity Coordinate Y (Nom)	0.42
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	140 lm/W
Color rendering index (CRI)	-
Arc Length O (Nom)	83 mm


Operating and Electrical	
Power Consumption	397.0 W
Voltage (Nom)	98 V
Voltage (Nom)	98 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T46
Approval and Application	
Energy Efficiency Class	E
Mercury (Hg) Content (Max)	19.6 mg
Mercury (Hg) Content (Nom)	19.6 mg

MASTER SON-T APIA Plus Xtra

Energy Consumption kWh/1000 h	397 kWh
EPREL Registration Number	473378
Product Data	
Order product name	MST SON-T APIA Plus Xtra 400W E40 1SL/12
Full product name	MASTER SON-T APIA Plus Xtra 400W E40 1SL/12
Full product code	872790092741200
Order code	92741200


Material Nr. (12NC)	928150519227
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900927412
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900927429

Dimensional drawing




Product	D (max)	O	L	C (max)
MST SON-T APIA Plus Xtra 400W E40 1SL/12	48 mm	83 mm	175 mm	283 mm

Photometric data




Light Distribution Diagram - MST SON-T APIA Plus Xtra 400W E40 1SL/12




Spectral Power Distribution Colour - MST SON-T APIA Plus Xtra 400W E40 1SL/12

MASTER SON-T APIA Plus Xtra

Lifetime



Life Expectancy Diagram - MST SON-T APIA Plus Xtra 400W E40 1SL/12



Lumen Maintenance Diagram - MST SON-T APIA Plus Xtra 400W E40 1SL/12

