



HORTI

MASTER GreenPower Xtra 1000W EL/5X6CT

High Pressure Sodium lamp with clear outer bulb, optimized growthlight output and maintenance

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information			
Cap-Base	K12x30s		
Operating Position	P [Parallel or Horizontal(HOR)]		
Light Technical			
Color Code	220 [CCT of 2000K]		
Chromaticity Coordinate X (Nom)	0.537		
Chromaticity Coordinate Y (Nom)	0.427		
Correlated Color Temperature (Nom)	2000 K		
Luminous Efficacy (rated) (Nom)	155 lm/W		
Color rendering index (CRI)	33		
Arc Length O (Nom)	147 mm		
Operating and Electrical			
Power Consumption	1,020.0 W		
Voltage (Nom)	220 V		
Voltage (Nom)	220 V		


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T40
Approval and Application	
Mercury (Hg) Content (Nom)	35 mg
Energy Consumption kWh/1000 h	1020 kWh
Product Data	
Order product name	MASTER GreenPower Xtra 1000W EL/5X6CT
Full product name	MASTER GreenPower Xtra 1000W EL/5X6CT
Full product code	871869682951600
Order code	342170
Material Nr. (12NC)	928152419216
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696829516
Numerator - Packs per outer box	30

Datasheet, 2023, April 14 data subject to change

EAN/UPC - Case


8718696829530

Dimensional drawing



Product	D (max)	0	C (max)	Α
MASTER GreenPower Xtra 1000W EL/5X6CT	33.5 mm	147 mm	394 mm	325 mm

Photometric data



Spectral Power Distribution Colour - MASTER GreenPower Xtra 1000W EL/5X6CT



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.