



# MASTER CityWhite CDO-ET



# MASTER CityWhite CDO-ET Plus 100W/828 E40

Ceramic metal halide lamp, with opalized ovoid outer bulb shape, used in outdoor offering pleasant white light

### **Warnings and Safety**

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- $\boldsymbol{\cdot}$  The luminaire must be able to contain hot lamp parts if the lamp ruptures
- $\cdot$  Lamps may use electronic or electromagnetic control gear
- · Control gear must include end-of-life protection (IEC61167, IEC 62035)

### **Product data**

General Information	
Cap base	E40 [E40]
Operating position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	27,000 h
Light Technical	
Colour Code	828 [CCT of 2800K]
Luminous Flux	9,400 lm
Colour designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.447
Chromaticity Coordinate Y (Nom)	0.4
Correlated Colour Temperature	2800 K
Luminous efficacy (rated) (nom.)	99 lm/W
Colour rendering index (CRI)	87

Operating and Electrical	
Power Consumption	95.0 W
Voltage (nom.)	90 V
Voltage (nom.)	90 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Coated glass
Bulb shape	B75 [B 75 mm]
Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) content (max.)	12 mg
Mercury (Hg) content (nom.)	11.6 mg
Energy consumption kWh/1,000 hours	95 kWh


Datasheet, 2023, April 14 data subject to change

# **MASTER CityWhite CDO-ET**

EPREL registration number	473399	
Product Data		
Order product name	MASTER CityWh CDO-ET Plus 100W/828 E40	
Full product name	MASTER CityWhite CDO-ET Plus 100W/828 E40	
Full EOC	871829115877600	
Order code	15877600	
Material no. (12 NC)	928154808835	


Local order code	100CDOETPLUS828
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718291158776
Numerator – packs per outer box	12
EAN/UPC - Case	8718291158783

## Dimensional drawing




Product	D (max)	C (max)
MASTER CityWh CDO-ET Plus 100W/828 E40	76 mm	186 mm

# Photometric data




Light Distribution Diagram - MASTER CityWh CDO-ET Plus 100W/828 E40




Spectral Power Distribution Colour - MASTER CityWh CDO-ET Plus 100W/828 E40

# **MASTER CityWhite CDO-ET**

### Lifetime





Life Expectancy Diagram - MASTER CityWh CDO-ET Plus 100W/828 E40

Lumen Maintenance Diagram - MASTER CityWh CDO-ET Plus 100W/828 E40

