



MASTER CityWhite CDO-ET



MASTER CityWhite CDO-ET Plus 150W/828 E40

Ceramic metal halide lamp, with opalized ovoid outer bulb shape, used in outdoor offering pleasant white light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)

Product data

General Information	
Cap base	E40
Operating position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	27,000 h
Light Technical	
Colour Code	828 [CCT of 2800K]
Luminous Flux	15,400 lm
Colour designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.447
Chromaticity Coordinate Y (Nom)	0.4
Correlated Colour Temperature	2800 K
Luminous efficacy (rated) (nom.)	108 lm/W
Colour rendering index (CRI)	85


Operating and Electrical	
Power Consumption	143.0 W
Voltage (nom.)	89 V
Voltage (nom.)	89 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Coated glass
Bulb shape	BD90 [BD 90 mm]
Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) content (max.)	15.8 mg
Mercury (Hg) content (nom.)	15.8 mg
Energy consumption kWh/1,000 hours	143 kWh

MASTER CityWhite CDO-ET

EPREL registration number	473400
Product Data	
Order product name	MASTER CityWh CDO-ET Plus 150W/828 E40
Full product name	MASTER CityWhite CDO-ET Plus 150W/828 E40
Full EOC	871829115881300
Order code	15881300
Material no. (12 NC)	928154908835


Local order code	150CDOETPLUS828
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291158813
Numerator – packs per outer box	12
EAN/UPC – Case	8718291158820

Dimensional drawing




Product	D (max)	C (max)
MASTER CityWh CDO-ET Plus 150W/828 E40	91 mm	227 mm

Photometric data




Light Distribution Diagram - MASTER CityWh CDO-ET Plus 150W/828 E40




Spectral Power Distribution Colour - MASTER CityWh CDO-ET Plus 150W/828 E40

MASTER CityWhite CDO-ET

Lifetime



Life Expectancy Diagram - MASTER CityWh CDO-ET Plus 150W/828 E40



Lumen Maintenance Diagram - MASTER CityWh CDO-ET Plus 150W/828 E40

