



# MSR

# MSR 575/2 10H 1CT/4

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

#### Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## **Product data**

General Information		Arc Length O (Nom)	7.0 mm
Cap-Base	GX9.5		
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 50% Failures (Nom)	1,000 hour(s)	Power Consumption	575 W
		Lamp Current (Nom)	6.75 A
Light Technical			
Color Code	2	Controls and Dimming	
Luminous Flux	47,000 lm	Dimmable	No
Chromaticity Coordinate X (Nom)	302		
Chromaticity Coordinate Y (Nom)	320	Product Data	
Correlated Color Temperature (Nom)	6990 K	Order product name	MSR 575/2 10H 1CT/4
Luminous Efficacy (Rated) (Min)	75 lm/W	Full product name	MSR 575/2 10H 1CT/4
Luminous Efficacy (rated) (Nom)	82 lm/W	Full product code	871829122127200
Color rendering index (CRI)	73	Order code	22127200
		Material Nr. (12NC)	928171605115

Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	8718291221272				
Numerator - Packs per outer box	4				


EAN/UPC - Case	8718291221289
_	

## **Dimensional drawing**



Product	D (max)	0	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575/2	30 mm	7.0	64 mm	66 mm	65	125 mm	36 mm	35	34 mm
10H 1CT/4		mm			mm			mm	

#### Photometric data



Spectral Power Distribution Colour - MSR 575/2 10H 1CT/4



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.