



Architectural MSD

MSD 1200.1CT/3

The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information						
Cap-Base	G22					
Operating Position	UNIVERSAL [Any or Universal (U)]					
Life to 50% Failures (Nom)	2,000 hour(s)					
Light Technical						
Color Code	- [Not Specified]					
Luminous Flux	92,000 lm					
Chromaticity Coordinate X (Nom)	323					
Chromaticity Coordinate Y (Nom)	328					
Correlated Color Temperature (Nom)	6000 K					
Luminous Efficacy (rated) (Nom)	79 lm/W					
Color rendering index (CRI)	73					
Arc Length O (Nom)	14.0 mm					
Operating and Electrical						
Power Consumption	1,200 W					

Lamp Current (Nom)	13.8 A				
Controls and Dimming					
Dimmable	No				
Product Data					
Order product name	MSD 1200.1CT/3				
Full product name	MSD 1200.1CT/3				
Full product code	872790091135000				
Order code	928172005114				
Material Nr. (12NC)	928172005114				
Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	8727900911350				
Numerator - Packs per outer box	3				
EAN/UPC - Case	8727900911367				

Datasheet, 2024, January 19 data subject to change


Architectural MSD

Dimensional drawing



Product	D (max)	0	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD	42.5	14.0	84 mm	86 mm	85	183 mm	54 mm	53	52 mm
1200.1CT/3	mm	mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSD 1200.1CT/3



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.