



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold 575/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information					
Cap-Base	PGJX28				
Operating Position	UNIVERSAL [Any or Universal (U)]				
Life to 50% Failures (Nom)	750 hour(s)				
Light Technical					
Color Code	2				
Luminous Flux	36,800 lm				
Chromaticity Coordinate X (Nom)	296				
Chromaticity Coordinate Y (Nom)	315				
Correlated Color Temperature (Nom)	7500 K				

Luminous Efficacy (rated) (Nom)	64 lm/W	
Color rendering index (CRI)	70	
Arc Length O (Nom)	3.5 mm	
Operating and Electrical		
Power Consumption	575 W	
Lamp Current (Nom)	10.2 A	
Controls and Dimming		
Dimmable	Yes	


Datasheet, 2024, January 18 data subject to change

MSR Gold™ MiniFastFit (Touring/Stage)

Product Data	
Order product name	MSR Gold 575/2 MiniFastFit 1CT/4
Full product name	MSR Gold 575/2 MiniFastFit 1CT/4
Full product code	871829122109800
Order code	928184005115
Material Nr. (12NC)	928184005115


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221098
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221104

Dimensional drawing



Product	D	0	L (min)	L (max)	L	С	F (max)	F	F (min)
	(max)					(max)			
MSR Gold	23.2	3.5	55 mm	57 mm	56	112 mm	36.5	36	35.3
575/2	mm	mm			mm		mm	mm	mm
MiniFastFit									
1CT/4									

Photometric data



Spectral Power Distribution Colour - MSR Gold 575/2 MiniFastFit 1CT/4



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.