



MASTERColour CDM-TC Elite

MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12

Single-ended, compact size, high-efficiency Ceramic Metal Halide discharge lamp

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G8.5
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	20,000 h

Light Technical	
Color Code	930 [CCT of 3000K]
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.435
Chromaticity Coordinate Y (Nom)	0.396
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	107 lm/W
Color rendering index (CRI)	90
Arc Length O (Nom)	7.15 mm

Operating and Electrical	
Power Consumption	73.2 W
Voltage (Nom)	85 V
Voltage (Nom)	85 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T14


Approval and Application	
Mercury (Hg) Content (Nom)	6.6 mg

MASTERC colour CDM-TC Elite

Energy Consumption kWh/1000 h	80 kWh
Product Data	
Order product name	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12
Full product name	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12
Full product code	871869648471500
Local code description	CDMTCEL70W930
Order code	928189505129


Material Nr. (12NC)	928189505129
Local order code	CDMTCEL70W930
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696484715
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696484722

Dimensional drawing




Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	15 mm	7.15 mm	51 mm	53 mm	52 mm	85 mm

Photometric data




Light Distribution Diagram - MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12




Spectral Power Distribution Colour - MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12

MASTERC colour CDM-TC Elite

Lifetime



Lumen Maintenance Diagram - MASTER CDM-TC Elite 70W/930 G8.5 1CT/12



Life Expectancy Diagram - MASTER CDM-TC Elite 70W/930 G8.5 1CT/12

