



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold 700/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Correlated Color Temperature (Nom)	
Cap-Base	PGJX28	7200 K	
Operating Position	UNIVERSAL [Any or Universal (U)]	Luminous Efficacy (rated) (Nom)	
Life to 50% Failures (Nom)	750 hour(s)	69 lm/W	
Light Technical		Color rendering index (CRI)	
Color Code	2	75	
Luminous Flux (Min)	44,000 lm	Arc Length O (Nom)	
Luminous Flux	47,000 lm	3.8 mm	
Chromaticity Coordinate X (Nom)	300	Operating and Electrical	
Chromaticity Coordinate Y (Nom)	324	Power Consumption	
		700 W	
		Lamp Current (Nom)	
		10.2 A	

MSR Gold™ MiniFastFit (Touring/Stage)

Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR Gold 700/2 MiniFastFit 1CT/4
Full product name	MSR Gold 700/2 MiniFastFit 1CT/4
Full product code	871829122117300
Order code	928199905115


Material Nr. (12NC)	928199905115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221173
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221180

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 700/2 MiniFastFit 1CT/4	23.2 mm	3.8 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 700/2 MiniFastFit 1CT/4

