



# MASTER SON-T PIA Plus

## MSTSON-TPIA Plus 70W E27 1CT/12

High Pressure Sodium lamp with clear tubular outer bulb, high output and long reliable lifetime

### Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	28,000 h
Light Technical	
Color Code	220 [CCT of 2000K]
Luminous Flux	6,650 lm
Chromaticity Coordinate X (Nom)	0.54
Chromaticity Coordinate Y (Nom)	0.42
Correlated Color Temperature (Nom)	1900 K
Luminous Efficacy (rated) (Nom)	91 lm/W
Color rendering index (CRI)	-
Operating and Electrical	
Power Consumption	74.0 W


Voltage (Nom)	93 V
Voltage (Nom)	93 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T35
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	12.2 mg
Mercury (Hg) Content (Nom)	12.2 mg
Energy Consumption kWh/1000 h	73 kWh
EPREL Registration Number	1612144

MASTER SON-T PIA Plus

Product Data	
Order product name	MSTSON-TPIA Plus 70W E27 1CT/12
Full product name	MSTSON-TPIA Plus 70W E27 1CT/12
Full product code	871829118069200
Local code description	SONTPLUS70WES
Order code	928483200094
Material Nr. (12NC)	928483200094


Local order code	SONTPLUS70WES
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291180692
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291180708

Dimensional drawing




Product	D (max)	O	L	C (max)
MSTSON-TPIA Plus 70W E27 1CT/12	35.75 mm	42 mm	102 mm	156 mm

Photometric data




Light Distribution Diagram - MSTSON-TPIA Plus 70W E27 1CT/12




Spectral Power Distribution Colour - MSTSON-TPIA Plus 70W E27 1CT/12

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MSTSON-TPIA Plus 70W E27 1CT/12

## MASTER SON-T PIA Plus

