PHILIPS Lighting



Switch Start Metal Halide Standard

MH175/C/U/M 12PK

High performance, Long life and Superior light quality. A compact, energy efficient metal halide lamp that provides crisp, sparkling light wih long life and high efficiency.

Warnings and Safety

• R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data

General Information		Operating and Electrical	
Cap-Base	E26 [Single Contact Medium Screw]	Lamp Current (Nom)	1.5 A
Operating Position	UNIVERSAL [Any or Universal (U)]	Voltage (Nom)	132 V
Life to 50% Failures (Nom)	10,000 hour(s)	Voltage (Nom)	132 V
Light Technical		Mechanical and Housing	
Color Code	640 [CCT of 4000K]	Bulb Finish	Coated glass
Color Designation	Cool White (CW)	Bulb Material	Hard Glass
Chromaticity Coordinate X (Nom)	0.395	Bulb Shape	BD17
Chromaticity Coordinate Y (Nom)	0.390		
Luminous Efficacy (Rated) (Min)	72 lm/W	Approval and Application	
Luminous Efficacy (rated) (Nom)	80 lm/W	Energy Saving Product	Not Applicable
Color rendering index (CRI)	65	Mercury (Hg) Content (Max)	24.0 mg

Switch Start Metal Halide Standard

Product Data	
Order product name	MH175/C/U/M 12PK
Full product name	MH175/C/U/M 12PK
Order code	928601122403
Material Nr. (12NC)	928601122403
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	046677313593
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677313598

Dimensional drawing

Product	D	C (max)
MH175/C/U/M 12PK	2.125 inch	5.438 inch





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.