

Fortimo LED linear light module

Fortimo LED LLM 3000/740 24W Gen4

The Fortimo LED linear light module (LLM) system represents a breakthrough in energy-efficient LED lighting for urban and residential applications. Cutting-edge LED technology ensures peak performance, delivering energy savings with Constant Light Output without compromising on light quality and comfort. Fortimo LED LLM offers a diffused white light LED alternative to traditional frosted light sources such as (compact) fluorescent, high-pressure mercury (HPL) and high-pressure sodium (SON) lamps. Designed primarily for residential outdoor lighting applications, this reliable, upgradeable solution is also suitable for many professional indoor applications. Fortimo LED LLM is a Green Product, contains no mercury and is fully RoHS-compliant.

Product data

General Information	
Lighting Technology	LED

Light Technical	
Color Code	740 [CCT of 4000K]
Luminous Flux	3,000 lumen
Color Designation	Neutral White
Color Consistency Initial	5
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	122 lm/W
Color rendering index (CRI)	73
LLMF At End Of Nominal Lifetime (Nom)	80 %

Operating and Electrical	
Power Consumption	24 W

Temperature	
Ambient temperature range	-20 °C to 55 °C
T-Case Lifetime (Nom)	65 °C
T-Case Maximum (Nom)	75 °C

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Approval Marks	CE marking ENEC certificate RoHS compliance REACH compliance

Fortimo LED linear light module

Product Data	
Full product code	871869643073600
Order product name	Fortimo LED LLM 3000/740 24W Gen4
Order code	929000941906
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

Material Nr. (12NC)	929000941906
Full product name	Fortimo LED LLM 3000/740 24W Gen4
EAN/UPC - Case	8718696430743
EAN/UPC - Product/Case	8718696430736

Dimensional drawing



Product	D1	C1	A1	A2	B1
Fortimo LED LLM 3000/740 24W Gen4	4.5 mm	40.5 mm	230.0 mm	214.5 mm	43.0 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.