



Essential LED tubes T5 Mains

MASTER LEDtube 1200mm 13W840 G5 I

The Essential LEDtube T5 is an affordable LED solution suitable for replacing T5 fluorescent lamps. Thanks to a unique design, Philips Essential LED tube T5 Mains can be directly installed in luminaires operating on mains power connection. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap base	G5 [G5]
Nominal lifetime (nom.)	40000 h
Switching cycle	50000X
Light Technical	
Colour Code	840 [CCT of 4,000 K]
Technical Beam Angle (Nom)	160 °
Lamp Luminous Flux 25°C EL (Nom)	1600 lm
Colour Temperature, horizontal (Nom)	4000 K
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	83
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	13 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9

Voltage (Nom)	33 V
Temperature	
T ambient (max.)	45 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product length	1200 mm
Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Suitable for accent lighting	No

Essential LED tubes T5 Mains

Approval marks	RoHS compliance KEMA Keur certificate CE marking
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Full product code	694793910873200
Order product name	MASTER LEDtube 1200mm 13W840 G5 I
EAN/UPC – product	6947939108732



Order code	929001131110
Numerator – quantity per pack	1
Numerator – packs per outer box	20
Material no. (12NC)	929001131110
Net weight (piece)	0.155 kg

Dimensional drawing

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm 13W840 G5 I	15.8 mm	21.0 mm	1148.0 mm	1155.0 mm	1162.0 mm


TLED T5 1200mm 13W DC 400mA 33V 4000K

Photometric data



LED Lamps, LEDtubes, MASTER LEDtube 1200mm 13W 4000K G5 I

LED Lamps, LEDtubes, MASTER LEDtube 1200mm 13W 4000K G5 I



Essential LED tubes T5 Mains

