



MASTER LEDbulb

MASTER LEDbulb DT 6-40W E27 A60 CL

The MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. They are particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimizes maintenance cost without any compromise on light quality. They can be used together with most leading-edge dimmers, enabling further efficiencies while helping to create the desired atmosphere.

Product data

General Information	
Cap base	E27 [E27]
Red Dot Design Award winner mark	Reddot Design Award Winner 2016
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	6-40W
Light Technical	
Colour code	822-827 [tunable warm white]
Luminous flux (nom.)	470 lm
Colour designation	Warm White (WW)
Correlated colour temperature (nom.)	2200-2700 K
Luminous efficacy (rated) (nom.)	78.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	6 W
Lamp current (nom.)	37 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	85 °C
Controls and Dimming	
Dimmable	Yes

MASTER LEDbulb

Mechanical and Housing

Bulb finish	Clear
-------------	-------

Approval and Application

Energy efficiency label (EEL)	A+
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	6 kWh


Product Data

Full product code	871869648128800
-------------------	-----------------

Order product name	MASTER LEDbulb DT 6-40W E27 A60 CL
EAN/UPC – product	8718696481288
Order code	48128800
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001150802
Net weight (piece)	0.076 kg

Warnings and Safety

Dimensional drawing





LED DT 6-40W E27 A60 CL

Product

MASTER LEDbulb DT 6-40W E27 A60 CL

Photometric data



MASTER LEDbulb

