



Essential LED tubes T5 Mains

MASTER LEDtube 600mm 7.5W865 G5 I

The Essential LEDtube T5 is an affordable LED solution suitable for replacing T5 fluorescent lamps. Thanks to a unique design, Philips Essential LED tube T5 Mains can be directly installed in luminaires operating on mains power connection. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data


General Information		Power Factor (Nom)		0.9
Cap-Base	G5 [G5]	Voltage (Nom)		19 V
EU RoHS compliant	Yes			
Nominal Lifetime (Nom)	40000 h	Temperature		
Switching Cycle	50000X	T-Ambient (Max)		45 °C
		T-Ambient (Min)		-20 °C
		T-Storage (Max)		65 °C
		T-Storage (Min)		-40 °C
		T-Case Maximum (Nom)		60 °C
Light Technical		Controls and Dimming		
Color Code	865 [CCT of 6500K]	Dimmable		No
Beam Angle (Nom)	160 °			
Luminous Flux (Nom)	800 lm	Mechanical and Housing		
Correlated Color Temperature (Nom)	6500 K	Product Length		600 mm
Color Consistency	<6			
Color Rendering Index (Nom)	83	Approval and Application		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Efficiency Label (EEL)		A+
		Energy Saving Product		Yes
		Suitable For Accent Lighting		No
Operating and Electrical				
Input Frequency	50 to 60 Hz			
Power (Rated) (Nom)	7.5 W			
Starting Time (Nom)	0.5 s			
Warm Up Time to 60% Light (Nom)	0.5 s			

Essential LED tubes T5 Mains

Approval Marks	RoHS compliance KEMA Keur certificate CE marking
Energy Consumption kWh/1000 h	9 kWh
Product Data	
Full product code	694793910976000
Order product name	MASTER LEDtube 600mm 7.5W865 G5 I
EAN/UPC - Product	6947939109760

Order code	929001155010
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	929001155010
Net Weight (Piece)	0.076 kg


Dimensional drawing




TLED T5 19V 7.5W-14W 800lm160D 6500K G5

Product	D1	D2	A1	A2	A3
MASTER LEDtube 600mm 7.5W865 G5 I	15.8 mm	21.0 mm	548.0 mm	555.0 mm	562.0 mm


Photometric data



LED Lamps, LEDtubes, MASTER LEDtube 600mm 7.5W 6500K G5 I



LED Lamps, LEDtubes, MASTER LEDtube 600mm 7.5W 6500K G5 I



VLE 1500 mm 23 W /865 ROT

Essential LED tubes T5 Mains

