



CorePro Plastic LEDcandles & lusters

CorePro LEDcandle ND 4-25W E14 827 B35 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	62.50 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz


Power Consumption	4 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35 [B 35mm]

CorePro Plastic LEDcandles & lusters

Approval and Application	
Energy Consumption kWh/1000 h	4 kWh
Product Data	
Order product name	CorePro candle ND 4-25W E14 827 B35 FR
Full product name	CorePro LEDcandle ND 4-25W E14 827 B35 FR
Full product code	871829178701300
Order code	78701300



Material Nr. (12NC)	929001157402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291787013
Numerator - Packs per outer box	10
EAN/UPC - Case	8718291787020

Dimensional drawing




Product	D	C
CorePro candle ND 4-25W E14 827 B35 FR	35 mm	106 mm

Photometric data



General uniform lighting - CorePro candle ND 4-25W E14 827 B35 FR


Light Distribution Diagram - CorePro candle ND 4-25W E14 827 B35 FR




Spectral Power Distribution Colour - CorePro candle ND 4-25W E14 827 B35 FR

CorePro Plastic LEDcandles & lusters

Lifetime



Life Expectancy Diagram - CorePro candle ND 4-25W E14 827 B35 FR



Lumen Maintenance Diagram - CorePro candle ND 4-25W E14 827 B35 FR

