



MASTER LEDspot LV AR111

MAS LEDspotLV D 11-50W 927 AR111 24D

With its new perfect-fit design, the Master LEDspot LV AR111 now works with most of G53 luminaires as a true retrofit solution. The lamp creates a brilliant visual effect for retail and hospitality applications such as shops, showrooms and galleries. The high quality light brings out the true colors in merchandise and emphasizes its beauty. It also lasts long, with a strong lumen and color maintenance. The beautifully designed lamp offers a well-defined beam with a multitude of beam angles to suit various applications. Not only does it employ the Philips patented solution to ensure it is compatible with a broad selection of standard 12V halogen electronic transformers, it also delivers high beam intensity which equivalent to halogen AR111 spots of 50W, 75W or 100W.

Product data

General Information		Color Consistency	
Cap-Base	G53 [G53]	Color Rendering Index (Nom)	90
EU RoHS compliant	Yes	LLMF At End Of Nominal Lifetime (Nom)	70 %
Nominal Lifetime (Nom)	40000 h	Luminous Flux in 90° Cone (Rated)	560 lm
Switching Cycle	50000X	Operating and Electrical	
Technical Type	11-50W	Power (Nom)	11 W
Light Technical		Lamp Current (Nom)	1300 mA
Color Code	927	Wattage Equivalent	50 W
Beam Angle (Nom)	24°	Starting Time (Nom)	0.5 s
Luminous Flux (Nom)	560 lm	Warm Up Time to 60% Light (Nom)	0.5 s
Luminous Intensity (Nom)	2900 cd	Power Factor (Nom)	0.7
Color Designation	Warm White (WW)	Voltage (Nom)	12 V
Correlated Color Temperature (Nom)	2700 K		
Luminous Efficacy (rated) (Nom)	50.91 lm/W		

MASTER LEDspot LV AR111

Temperature

T-Case Maximum (Nom)	70 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----


Approval and Application

Energy Efficiency Label (EEL)	A
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	13 kWh

Product Data

Full product code	871869651488700
Order product name	MAS LEDspotLV D 11-50W 927 AR111 24D
EAN/UPC - Product	8718696514887
Order code	929001169802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001169802
Net Weight (Piece)	0.160 kg

Dimensional drawing




LED D 11-50W 927 AR111 24D

Product

MAS LEDspotLV D 11-50W 927 AR111 24D

Photometric data




Accent Lighting - Spots

CalcLux Prosimetrics 4.5

Philips Lighting B.V.


Page 1/17





MASTER LEDspot LV AR111 50W G53 927 24D

MASTER LEDspot LV AR111

Photometric data



Lifetime



MASTER LEDspotLV AR111 75W G53 940 40D

MASTER LEDspotLV AR111 75W G53 940 40D

