



CorePro Plastic LEDbulbs



CorePro LEDbulb ND 10-75W A60 E27 840

CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	1,055 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	105.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Lamp Current (Nom)	95 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A60

CorePro Plastic LEDbulbs


Approval and Application	
Energy Efficiency Class	F
Energy Consumption kWh/1000 h	10 kWh
EPREL Registration Number	397631
EyeComfort	Yes

Application Conditions	
can it be used in closed luminaires	No

Product Data	
Order product name	CorePro LEDbulb ND 10-75W A60 E27 840



Full product name	CorePro LEDbulb ND 10-75W A60 E27 840
Full product code	871869651032200
Order code	51032200
Material Nr. (12NC)	929001234802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696510322
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696510339

Dimensional drawing



Product	D	C
CorePro LEDbulb ND 10-75W A60 E27 840	60 mm	110 mm

Photometric data




General uniform lighting - CorePro LEDbulb ND 10-75W A60 E27 840

Light Distribution Diagram - CorePro LEDbulb ND 10-75W A60 E27 840


CorePro Plastic LEDbulbs

Photometric data




Spectral Power Distribution Colour - CorePro LEDbulb ND 10-75W A60 E27 840

Lifetime



Life Expectancy Diagram - CorePro LEDbulb ND 10-75W A60 E27 840



Lumen Maintenance Diagram - CorePro LEDbulb ND 10-75W A60 E27 840

