



CorePro Plastic LEDbulbs



CorePro LEDbulb ND 13-100W A60 E27 830

The CorePro LED bulb is the perfect bulb for your basic lighting needs. It provides beautiful light and dependable performance you expect from LED at an affordable price. CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings of 80% and provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	1,521 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	117 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	13 W
Lamp Current (Nom)	120 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	No

CorePro Plastic LEDbulbs


Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A60
Approval and Application	
Energy Efficiency Class	E
Energy Consumption kWh/1000 h	13 kWh
EPREL Registration Number	397632
EyeComfort	Yes
Application Conditions	
can it be used in closed luminaires	No

Product Data	
Order product name	CorePro LEDbulb ND 13-100W A60 E27 830
Full product name	CorePro LEDbulb ND 13-100W A60 E27 830
Full product code	871869657767700
Order code	929001235002
Material Nr. (12NC)	929001235002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696577677
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696577684


Dimensional drawing

Product	D	C
CorePro LEDbulb ND 13-100W A60 E27 830	60 mm	110 mm

Photometric data




General uniform lighting - CorePro LEDbulb ND 13-100W A60 E27 830



Light Distribution Diagram - CorePro LEDbulb ND 13-100W A60 E27 830


CorePro Plastic LEDbulbs

Photometric data




Spectral Power Distribution Colour - CorePro LEDbulb ND 13-100W A60 E27 830

Lifetime



Life Expectancy Diagram - CorePro LEDbulb ND 13-100W A60 E27 830



Lumen Maintenance Diagram - CorePro LEDbulb ND 13-100W A60 E27 830

