



# CorePro LEDcapsule LV

## CorePro LEDcapsuleLV 2-20W G4 827 D

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs without any compromise on light quality.

### Product data


<b>General Information</b>		<b>Power Consumption</b>	
Cap-Base	G4 [G4]	2 W	
Nominal lifetime	15,000 hour(s)	<b>Lamp Current (Nom)</b>	
Switching Cycle	50,000	220 mA	
Lighting Technology	LED	<b>Wattage Equivalent</b>	
EU RoHS compliant	Yes	20 W	
<b>Light Technical</b>		<b>Starting Time (Nom)</b>	
Color Code	827 [CCT of 2700K]	0.5 s	
Luminous Flux	200 lm	<b>Warm-up time to 60% light</b>	
Color Designation	Warm White (WW)	0.5 s	
Correlated Color Temperature (Nom)	2700 K	<b>Power Factor (Fraction)</b>	
Luminous Efficacy (rated) (Nom)	100.00 lm/W	0.7	
Color Consistency	<6	<b>Voltage (Nom)</b>	
Color rendering index (CRI)	80	12 V	
LLMF At End Of Nominal Lifetime (Nom)	70 %	<b>Temperature</b>	
<b>Operating and Electrical</b>		<b>T-Case Maximum (Nom)</b>	
Line Frequency	- Hz	84 °C	
Input Frequency	- Hz	<b>Controls and Dimming</b>	
		<b>Dimmable</b>	
		Yes	
		<b>Mechanical and Housing</b>	
		<b>Bulb Shape</b>	
		Capsule	
		<b>Approval and Application</b>	
		<b>Energy Saving Product</b>	
		Yes	
		<b>Suitable For Accent Lighting</b>	
		Yes	

CorePro LEDcapsule LV

Energy Consumption kWh/1000 h	3 kWh
Product Data	
Order product name	CorePro LEDcapsuleLV 2-20W G4 827 D
Full product name	CorePro LEDcapsuleLV 2-20W G4 827 D
Full product code	871869657865000
Order code	57865000

Material Nr. (12NC)	929001235302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696578650
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696578667

Dimensional drawing




Product	D	C
CorePro LEDcapsuleLV 2-20W G4 827 D	17 mm	48 mm


Photometric data



Spectral Power Distribution Colour - CorePro LEDcapsuleLV 2-20W G4 827 D



General uniform lighting - CorePro LEDcapsuleLV 2-20W G4 827 D



Light Distribution Diagram - CorePro LEDcapsuleLV 2-20W G4 827 D

## CorePro LEDcapsule LV

