



# SceneSwitch LED bulbs

## LED Scene Switch 60W A60 E27 WW FR ND 1SRT4

Some situations call for cool light, others benefit from the ambience of a warm, cosy glow. With Philips SceneSwitch LEDbulbs, you can have different light settings from just one bulb. And you don't need a dimmer! Optimise your lighting for relaxing, hobbies, recreation or working. Simply, at the flick of a switch. And that's your existing switch! No extra installation is required.

### Product data

General Information	
Cap base	E27 [ E27]
RoHS mark	RoHS mark
Nominal lifetime (nom.)	15000 h
Switching cycle	100000X
Technical Type Setting(s)	8-5-2-60 W
Light Technical	
Colour code	827/825/822 [ CCT of 2,700 K/2,500 K/2,200 K]
Luminous Flux Setting(s)	806-320-80 lm
Luminous Flux (Rated) Setting(s)	806-320-80 lm
Colour designation	Warm/Extra Warm/Very Warm
Correlated Color Temperature Setting(s)	2700/2500/2200 K
Luminous efficacy (rated) (nom.)	100.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) Setting(s)	8-5-2 W
Lamp current (nom.)	100 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Frosted

# SceneSwitch LED bulbs

## Approval and Application


Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	8 kWh

## Product Data

Full product code	871869658884002
Order product name	LED Scene Switch 60W A60 E27 WW FR ND 1SRT4

EAN/UPC – product	8718696588840
Order code	58884002
Numerator – quantity per pack	1
Numerator – packs per outer box	4
Material no. (12NC)	929001236558
Net weight (piece)	0.060 kg


## Dimensional drawing




SS Bulb 9.5W-60W 150D 2700-2200K E27 ND

Product	D	C
LED Scene Switch 60W A60 E27 WW FR ND 1SRT4	61 mm	111 mm


## Photometric data




LED Lamps, SceneSwitch ND 60W A60S /822



LED Lamps, SceneSwitch ND 60W A60S /825



LED Lamps, SceneSwitch ND 60W A60S /827



SceneSwitch ND 60W A60S

## SceneSwitch LED bulbs

### Photometric data



SceneSwitch ND 60W A60

### Lifetime

