



# Classic filament LEDbulbs

## LEDClassic 2-25W P45 E27 WW CL ND APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	125.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	2 W
Lamp Current (Nom)	20 mA

Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	70 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]

Approval and Application	
Energy Consumption kWh/1000 h	2 kWh


Product Data	
Order product name	LEDClassic 2-25W P45 E27 WW CL ND APR
Full product name	LEDClassic 2-25W P45 E27 WW CL ND APR

Classic filament LEDbulbs

Full product code	871869657433100
Order code	929001238708
Material Nr. (12NC)	929001238708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574331


Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574348

Dimensional drawing




Product	D	C
LEDClassic 2-25W P45 E27 WW CL ND APR	45 mm	78 mm


Photometric data



Spectral Power Distribution Colour - LEDClassic 2-25W P45 E27 WW CL ND APR




Light Distribution Diagram - LEDClassic 2-25W P45 E27 WW CL ND APR




General uniform lighting - LEDClassic 2-25W P45 E27 WW CL ND APR

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic 2-25W P45 E27 WW CL ND APR



Lumen Maintenance Diagram - LEDClassic 2-25W P45 E27 WW CL ND APR

