



MASTER LEDspot ExpertColor LV

MAS LED MR16 ExpertColor 8-50W 940 36D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Product data


General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Cap-Base	GU5.3 [GU5.3]		
Nominal lifetime	40,000 hour(s)		
Switching Cycle	50,000		
Lighting Technology	LED		
EU RoHS compliant	Yes		
Light Technical		Operating and Electrical	
Color Code	940 [CCT of 4000K]	Line Frequency	- Hz
Beam Angle (Nom)	36 degree(s)	Input Frequency	- Hz
Luminous Flux	480 lm	Power Consumption	8 W
Luminous Intensity (Nom)	1,450 cd	Lamp Current (Nom)	800 mA
Color Designation	Cool White (CW)	Wattage Equivalent	50 W
Correlated Color Temperature (Nom)	4000 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	70.83 lm/W	Warm-up time to 60% light	1 s
Color Consistency	<3	Power Factor (Fraction)	0.7
Color rendering index (CRI)	97	Voltage (Nom)	12 V
		Temperature	
		T-Case Maximum (Nom)	92 °C

MASTER LEDspot ExpertColor LV

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	MAS LED MR16 ExpertColor 8-50W 940 36D



Full product name	MAS LED MR16 ExpertColor 8-50W 940 36D
Full product code	871869674020000
Order code	929001242768
Material Nr. (12NC)	929001242768
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696740200
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696740217

Dimensional drawing



Product	D	C
MAS LED MR16 ExpertColor 8-50W 940 36D	51 mm	46 mm

Photometric data




General uniform lighting - MAS LED MR16 ExpertColor 8-50W 940 36D

Light Distribution Diagram - MAS LED MR16 ExpertColor 8-50W 940 36D


MASTER LEDspot ExpertColor LV

Photometric data




Spectral Power Distribution Colour - MAS LED MR16 ExpertColor 8-50W 940 36D

Lifetime



Life Expectancy Diagram - MAS LED MR16 ExpertColor 8-50W 940 36D



Lumen Maintenance Diagram - MAS LED MR16 ExpertColor 8-50W 940 36D

