



LED PAR38

17PAR38/EXPERTCOLOR RETAIL/F40/930/DIM

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	1,200 lm
Luminous Intensity (Nom)	2,700 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	70 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	17 W
Lamp Current (Nom)	170 mA

Wattage Equivalent	120 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR38
UL Wet/ damp/ dry location	Damp location
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
T20 compliant	No

LED PAR38

Application Conditions


can it be used in closed luminaires No

Product Data

Order product name 17PAR38/EXPERTCOLOR RETAIL/
F40/930/DIM
Full product name 17PAR38/EXPERTCOLOR RETAIL/
F40/930/DIM


Order code 471011
Material Nr. (12NC) 929001285404
Numerator - Quantity Per Pack 1
EAN/UPC - Product/Case 046677471019
Numerator - Packs per outer box 6
EAN/UPC - Case 50046677471014

Dimensional drawing




Product	D	C
17PAR38/EXPERTCOLOR RETAIL/F40/930/DIM	120.7 mm	134.6 mm


Photometric data



Spectral Power Distribution Colour - 17PAR38/EXPERTCOLOR RETAIL/
F40/930/DIM





Accent Lighting Spots - 17PAR38/EXPERTCOLOR RETAIL/F40/930/DIM



Light Distribution Diagram - 17PAR38/EXPERTCOLOR RETAIL/
F40/930/DIM

LED PAR38

Lifetime



Life Expectancy Diagram - 17PAR38/EXPERTCOLOR RETAIL/F40/930/DIM

Lumen Maintenance Diagram - 17PAR38/EXPERTCOLOR RETAIL/
F40/930/DIM

