



LED PAR30 S/L

12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	880 lm
Luminous Intensity (Nom)	2,000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	73 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	12 W
Lamp Current (Nom)	120 mA


Wattage Equivalent	90 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR30L
UL Wet/ damp/ dry location	Damp location
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
T20 compliant	No

LED PAR30 S/L

Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	12PAR30L/EXPERTCOLOR RETAIL/ F40/930/DIM
Full product name	12PAR30L/EXPERTCOLOR RETAIL/ F40/930/DIM


Order code	471052
Material Nr. (12NC)	929001285804
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677471057
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677471052

Dimensional drawing




Product	D	C
12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM	94.8 mm	116.1 mm


Photometric data



Spectral Power Distribution Colour - 12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM




Accent Lighting Spots - 12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM




Light Distribution Diagram - 12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM

LED PAR30 S/L

Lifetime



Life Expectancy Diagram - 12PAR30L/EXPERTCOLOR RETAIL/
F40/930/DIM



Lumen Maintenance Diagram - 12PAR30L/EXPERTCOLOR RETAIL/
F40/930/DIM

