



Classic frosted LED Lamps

LED classic 75W A60 E27 WW FR ND 1CT/10

Featuring a classic heritage design, LED frosted Classic bulbs deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of the LED frosted Classic lamps are a perfect fit for your existing fixtures.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	30,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,055 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	124.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	8.5 W
Lamp Current (Nom)	65 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	50 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A60 [A 60mm]


Approval and Application	
Energy Consumption kWh/1000 h	9 kWh

Classic frosted LED Lamps

EyeComfort	Yes
Product Data	
Order product name	LED classic 75W A60 E27 WW FR ND 1CT/10
Full product name	LED classic 75W A60 E27 WW FR ND 1CT/10
Full product code	871869670555100
Order code	929001286331


Material Nr. (12NC)	929001286331
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696705551
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696705568

Dimensional drawing




Product	D	C
LED classic 75W A60 E27 WW FR ND 1CT/10	60 mm	110 mm


Photometric data



General uniform lighting - LED classic 75W A60 E27 WW FR ND 1CT/10




Spectral Power Distribution Colour - LED classic 75W A60 E27 WW FR ND 1CT/10




Light Distribution Diagram - LED classic 75W A60 E27 WW FR ND 1CT/10

Classic frosted LED Lamps

Lifetime



Lumen Maintenance Diagram - LED classic 75W A60 E27 WW FR ND 1CT/10



Life Expectancy Diagram - LED classic 75W A60 E27 WW FR ND 1CT/10

