PHILIPS

Lighting



Essential LEDtube

LEDtube HO 600mm 10W 730 T8 AP I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	730 [CCT of 3000K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	950 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	95.00 lm/W
Color Consistency	<7
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	65 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	600 mm
Bulb Shape	T8

Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	10 kWh


Product Data	
Order product name	LEDtube HO 600mm 10W 730 T8 AP I G
Full product name	LEDtube HO 600mm 10W 730 T8 AP I G

Essential LEDtube

Full product code	871869668766600
Order code	929001299908
Material Nr. (12NC)	929001299908
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696687666


Numerator - Packs per outer box	10
EAN/UPC - Case	8718696687673

Dimensional drawing




Product	D1	D2	A1	A2	A3
LEDtube HO 600mm 10W 730 T8 AP I G	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm


Photometric data



Spectral Power Distribution Colour - LEDtube HO 600mm 10W 730 T8 AP I G




Light Distribution Diagram - LEDtube HO 600mm 10W 730 T8 AP I G




General uniform lighting - LEDtube HO 600mm 10W 730 T8 AP I G


Lifetime




Life Expectancy Diagram - LEDtube HO 600mm 10W 730 T8 AP I G




Life Expectancy Diagram - LEDtube HO 600mm 10W 730 T8 AP I G



Life Expectancy Diagram - LEDtube HO 600mm 10W 730 T8 AP I G



Lumen Maintenance Diagram - LEDtube HO 600mm 10W 730 T8 AP I G



Lumen Maintenance Diagram - LEDtube HO 600mm 10W 730 T8 AP I G

Essential LEDtube

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com
2023, April 29 - data subject to change