



CorePro LEDbulbs

CorePro LED bulb ND 7.5-60W A60 E27 865

Delivering a warm, halogen-like accent beam, LEDspots are a perfect fit for spot lighting and have a broad compatibility with transformers. LEDspots are compatible with most existing fixtures with a GU10 / MR16 GU5.3 / E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs. LEDcandle and LEDcluster are compatible with existing fixtures with an E27/E14 holder and are designed for retrofit replacement of incandescent lamps. LEDlamps deliver huge energy savings and minimize maintenance cost

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	7.5-60W
Light Technical	
Colour Code	865 [CCT of 6,500 K]
Technical Beam Angle (Nom)	200 °
Lamp Luminous Flux 25°C EL (Nom)	806 lm
Lamp Luminous Flux (Nom)	806 lm
Colour Designation	Cool Daylight
Colour Temperature, horizontal (Nom)	6500 K
Lamp Luminous Efficacy EM (Nom)	107.00 lm/W
Colour consistency	<6
Colour Rendering Index, horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	7.5 W
Lamp current (nom.)	70 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	85 °C
Controls and Dimming	
Dimmable	No

CorePro LEDbulbs

Mechanical and Housing

Bulb finish	Frosted
-------------	---------

Approval and Application


Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	8 kWh

Product Data

Full product code	871869657785100
-------------------	-----------------

Order product name	CorePro LED bulb ND 7.5-60W A60 E27 865
EAN/UPC – product	8718696577851
Order code	929001304832
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001304832
Net weight (piece)	0.076 kg


Dimensional drawing




A60 220-240V 8W-60W 806lm 6500K E27 ND

Product	D	C
CorePro LED bulb ND 7.5-60W A60 E27 865	60 mm	110 mm

Photometric data




CorePro LEDbulb 60W E27 865 FR A60



CorePro LEDbulb 40W E27 865 FR A60


CorePro LEDbulbs

Photometric data




CorePro LEDbulb 40W E27 830 FR A60

Lifetime



LEDbulb 40W E27 830 FR A60



LEDbulb 40W E27 830 FR A60

